

Annunciator Room Display

Technical Specifications

Feature	Description
Height	111 mm (Australian plate)
Width	68 mm (Australian plate)
Depth	30 mm
Weight	80 grams
Mounting Method	Wall box
Wall Box Size	Standard Australian or North American
Temperature	0-50°C
Humidity Range	0-85% Non Condensing
Connectors	Screw terminal type
Cable Sizes	Typically 2 core (AWG22) 7/0.25 data + 2 core 1.5mm ² 12V power 4 core (AWG22) 7/0.25 data to AM-CSP
Current Consumption	Disabled in STBY: 25mA Enabled in STBY: 50mA Call Active: 80mA
Voltage	11Volt to 14Volt DC



© 2012 Austco Marketing & Service (Asia) Pte Ltd

All rights are reserved.

Austco Marketing & Service (Asia) Pte Ltd reserves the right to make changes in specifications and/or discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

Compliance

Designed to comply with:



- AS 3811:1998 Hard-wired patient alarm systems for hospitals.
- AS 2999:1989 Alarm systems for the elderly and other persons at risk.
- HTM 08-03: Bedhead services.
- UL 1069 Hospital Signaling and Nurse Call Equipment.
- C-Tick Electromagnetic compatibility.
- IEC 60601-1, UL 60601-1 and CAN/CSA C22.2 No. 601.1-M90: Medical electrical equipment - Part 1: General requirements for safety.
- CE Mark of European Conformity.

Manufactured in general accordance with the requirements of international quality assurance standard ISO9002.

Product Code

AN-RMD

Description

Annunciator Room Display

Order Options

Singapore
Blk 5014 Ang Mo Kio Avenue 5
#05-07/08 TECHplace II
SINGAPORE 569881

+65 6481 8400
+65 6481 9400
www.austco.com.sg

Authorised Austco Reseller