

PULL CORD CALLPOINTS



Water resistant, flush wall- or ceiling-mounted callpoints that initiate calls on the TACERA Nurse Call System. The cord has a wipe-clean surface and has its own Snapback™ strain relief to ensure reliable operation without any possibility of damage. Standard features include a reassurance LED, tone sounder for audibly or visually impaired patients and call mute mode for cleaners.

IPnet compatible and net- or web-configured
Clear colours and concise labels
Low activation force

LOWER “WHOLE-OF-LIFE” COSTS

Pull Cord Callpoints are IP-based and feature plug-and-play functionality. They are connected in series using only standard CAT5/6 cable that also provides POIPnet (Power Over IPnet).

Each callpoint has a unique MAC address and is supplied configured for immediate use. Once connected, the callpoint is quickly and easily assigned to a room using a web-browser, which simplifies the process and reduces the cost of installation and commissioning.

The system continuously checks the functionality of each device and will immediately notify maintenance staff if any problem is detected. Pull Cord Callpoints are hot-swappable, making maintenance a breeze – simply replace a callpoint and then use the web-browser to quickly re-assign functionality to the new device.

EASY TO IDENTIFY AND USE

These callpoints feature a pull cord with handle that is brightly coloured and clearly labelled with an icon for fast identification.

Users can easily initiate a call by pulling on the pull cord.

All callpoints are connected on the IPnet patient area

network to all other components of the TACERA system to initiate communication between nursing staff and patients.

WATER RESISTANT

Pull Cord Callpoints are typically installed in ensuites, toilets and other wet areas, so are supplied with a water resistant silicone rubber boot that ensures an IP 65 rating. The boot seals the callpoint at the back (where moisture ingress normally occurs) and between the wall plate and wall.

IMPROVED INFECTION CONTROL

These ergonomic callpoints are flush, wall- or ceiling-mounted with a pull cord that has a wipe-clean surface for improved infection control. Each wall-mounted Pull Cord Callpoint has a separate CANCEL button that illuminates red, giving visual reassurance that a call has been initiated. A separate Cancel Callpoint is required for ceiling-mounted Pull Cord Callpoints.

To avoid nuisance alarms during cleaning, the callpoint incorporates a cleaning mode. The cleaning time and date is logged on the central server, providing an important audit trail for infection control compliance.

- For safety and to improve reliability, the pull cord incorporates Snapback™ strain relief that will break apart with a load of more than 10 kg.
- Pull Cord Callpoints fit into standard electrical wall boxes, reducing installation times and costs.
- Manufactured from an impact-resistant polycarbonate / ABS plastic, all Pull Cord Callpoints feature concealed stainless steel fixings to maximise the life of the callpoint and reduce maintenance costs.
- Class B certification ensures the callpoints meet the new emission requirements for hospitals and aged care facilities.